Class I (\leq 2 ft³) and Class II (\leq 10 ft³)

Description

Model 1001A is an enclosure pressurization or purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed (protected) enclosure(s), in order to prevent combustible dust accumulation or remove and prevent flammable gas or vapor accumulations. In Class II areas, the system maintains a "safe" (1.0") pressure. In Class I areas, the system accomplishes four air exchanges and maintains a "safe" (0.25") pressure. These processes reduce the hazardous (classified) area rating within the enclosure(s), in accordance with the NEC - NFPA 70, Article 500, NFPA 496 and ISA 12.4.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. In Class II areas, all dust must be removed from the enclosure(s). The enclosure protection vent (if used) must be tested and enclosure(s) must be sealed. The enclosure pressure control regulator is then used to set a safe reading on the enclosure pressure gauge. In Class II areas, power can be energized when safe pressure is stable. In Class I areas, the user must perform an exchange cycle (determined by the safe pressure flow rate—five minutes minimum) before power can be energized. Loss of safe pressure in Class I or II areas requires immediate attention, unless power is deenergized. WPS style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems.

System Specifications

System Dimensions: See page 10 Shipping Weight: LPS - 5 lb / WPS - 10 lb Temp. Range: -20°F to +120°F * 5 - 120 psi Supply Pressure Range: Supply Requirements: Clean air or inert gas Safe Press. (CI/CII): 0.25"/1.0" Safe Press. Flow Rate: ** 0.1 - 3.5 SCFH System Supply Fitting: 1/4" tube fitting **Enclosure Supply Fitting:** 1/4" tube fitting 1/4" tube fitting Enclosure Reference Fitting: Switch Setting (CI/CII, Decr): 0.15"/0.5" ± 0.02" Switch Conduit Port Size: 1/2" FPT Switch Contact Rating

120 VAC. 15 A WPS Style: WPSA Style: *** 120 VAC, 10 A, 28 - 125 VDC

- With EPV-1 Vent 120 psi max. to 5 psi min. Systems installed without Vent must be equipped with redundant regulator set to 5 psi max.
- ** Enclosure integrity determines actual flow rate
- *** Supply voltages 24 VDC and 240 VAC available upon request.

Model 1001A



LPS Style (Less Pressure Switch)







WPS/WPSA Style (With Pressure Switch)

Standard Model Applications

Model Number: 1001A-CI Type Y Model Number: 1001A-CI Type Z Designation: Purging System Designation: **Enclosure Volume:** 2 ft³ max. Enclosure Volume: LPS Style LPS Style UL & FM Certified: Cl. I, Div. 1, UL & FM Certified: Group A-D

Rating Reduction: Div. 1 to Div. 2 **WPS Style**

> Cl. I, Div. 1, Group C&D

Rating Reduction: Div. 1 to Div. 2

UL & FM Certified:

WPSA Style

UL & FM Certified: Cl. I, Div. 1, Group A-D Rating Reduction: Div. 1 to Div. 2 **Purging System** 2 ft3 max.

Cl. I, Div. 2, Group A-D Div. 2 to Rating Reduction: Nonhazardous

WPS Style

UL & FM Certified: Cl. I, Div. 2, Group C&D Rating Reduction: Div. 2 to Nonhazardous

WPSA Style

UL & FM Certified: Cl. I, Div. 2, Group A-D Rating Reduction: Div. 2 to Nonhazardous

Model Number: 1001A-CII Type Y Designation: Pressurization System

Enclosure Volume: 10 ft³ max.

LPS Style

UL & FM Certified: CI. II, Div. 1, Group F&G

Rating Reduction: Div. 1 to Div. 2

WPS Style

UL & FM Certified: Cl. II, Div. 1, Group F&G Rating Reduction: Div. 1 to Div. 2 Model Number: 1001A-CII Type Z Designation: Pressurization System Enclosure Volume: 10 ft³ max.

LPS Style

UL & FM Certified: Cl. II, Div. 2, Group F&G

Div. 2 to Rating Reduction: Nonhazardous

WPS Style

UL & FM Certified: Cl. II, Div. 2, Group F&G

Rating Reduction: Div. 2 to Nonhazardous



SERIES

Descen

Pressure Gauge Enclosure Reference

Inlet Venturi

Orifice WPS Style

(With Pressure Switch)

TJ BERCO EPS

LPS Style (Less Pressure Switch)

e Outlet
Switch) Plate

System

Supply

Inlet

Enclosure

Pressure

Control

Regulator

Enclosure


Supply

CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM

Material Specifications

Regulator Body: Zinc w/Enamel Finish Regulator Handle: Polycarbonate **Enclosure Pressure Gauge:** Alum. w/Enamel Finish 316 SS Forged Body **Tube Fittings:** 316 SS 1/4" .035 Welded Tubing: Silk screened Lexan® & SS System Nameplates: Fastener Hardware: Alum. & Stainless Steel Mounting Plate: 316 14 Ga #3 Brush SS **EXP Pressure Switch Body:** Anodized Cast Alum. **Enclosure Warning Nameplate:** Silk screened SS Lexan® is a registered trademark of the General Electric Company

Model Number Designations



Model 1001A System Accessories (See accessories page for complete details)

FACTORY INSTALLED FITTINGS

ECK-1001A Enclosure Connection Kit
CONNECTION FITTINGS

EFC-4 1/4" Flush Connector
EBC-4 1/4" Bulkhead Connector
EPC-10 1/2" Pipe Connector
ADDITIONAL ITEMS

ILF-4 1/4" Filter SMK-1, -4 or -6 System Mounting Kit EPSK-1 or -2 Explosion Proof Switch Kit

GPSK-1 or -2 General Purpose Switch Kit
RAH Div. 1 Remote Alarm Horn
RAB-1 Div. 1 Remote Alarm Beacon
RAB-2 Div. 2 Remote Alarm Beacon
LCK L Fitting Conduit Kit
TCK T Fitting Conduit Kit

OPTIONAL ENCLOSURE PROTECTION VENTS

EPV-1-SA-00 Straight w/Spark Arrestor EPV-1-SA-90 Rt Angle w/Spark Arrestor

OPTIONAL HEX KEY REGULATOR HANDLE

TR-10G Tamper Proof Regulator

WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning
EWN-2 Class II Enclosure Warning
ETW Enclosure Temperature Warning

INSTALLATION & OPERATION MANUAL

129-0197 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

Overall System Dimensions						
LPS / WPS	LH - left hand	RH - right hand	TM - top mount	BM - bottom mount	WM - wall mount	FM & PM - surface
Height	7 / 12	7 / 12	7/8	7/8	7 / 12	9 / 14
Width	8 / 8	8 / 8	8 / 13.375	8 / 13.375	8/8	10 / 10
Depth	5.5 / 7.25	5.5 / 7.25	5.5 / 7.25	5.5 / 7.25	7.5 / 9.25	5 / 6.5

Dimensions in inches. Mounting dimensions available upon request. FM & PM panel cutout dimensions: LPS - 8h x 9w WPS - 13h x 9w Height & Width dimensions reflect mounting plate measurements. Depth dimension reflects overall measurement of system, including components.





Description

Model 1002 is a Rapid Exchange® purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed (protected) enclosure(s), in order to remove and prevent flammable gas or vapor accumulations. The system accomplishes four air exchanges and maintains a "safe" (0.25") pressure. A Pepperl+Fuchs Model EPV-2 Enclosure Protection Vent is required for proper operation. This process reduces the hazardous (classified) area rating within the enclosure(s), in accordance with the NEC - NFPA 70, Article 500, NFPA 496 and ISA 12.4.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. The enclosure protection vent must be tested and the enclosure(s) must be sealed. The enclosure pressure control valve is then used to set a safe reading on the enclosure pressure indicator. When safe pressure is stable, the Rapid Exchange® control valve must be fully engaged. Upon completion of the Rapid Exchange® cycle, (five minutes minimum) the Rapid Exchange® control valve must be disengaged to return to a safe enclosure pressure. Power can then be energized to the protected enclosure(s). Loss of safe pressure requires immediate attention, unless power is deenergized. WPS style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems.

Model 1002



LPS Style (Less Pressure Switch)



WPS/WPSA Style (With Pressure Switch)





System Specifications

System Dimensions: See page 16 Shipping Weight: LPS - 10 lb / WPS - 15 lb -20°F to +120°F Temp. Range: Supply Pressure Range: 80 - 120 psi Capacity & Filtration: 1.5 oz @ 20 Micron Supply Requirements: clean air or inert gas Safe Press. Setpoint: 0.25" Safe Press. Flow Rate: * 0.1 - 3.5 SCFH 3" - 5" Exchange Pressure: Exchange Flow Rate: ** 4 SCFM / 240 SCFH **Exchange Time:** 1 min/ft3 System Supply Port: 1/4" FPT **Enclosure Supply Fitting:** 1/4" tube fitting Enclosure Reference Fitting: 1/4" tube fitting Switch Setting (Decr): 0.15" ± 0.02" Switch Conduit Port Size: 1/2" FPT Switch Contact Rating

WPS Style: 120 VAC, 15 A WPSA Style: *** 120 VAC, 10 A, 28 - 125 VDC

- * Enclosure integrity determines actual flow rate
- ** With regulator set to 60 psi min. during exchange Rapid Exchange® is a Registered Trademark of PepperI+Fuchs, Inc.
- *** Supply voltages 24 VDC and 240 VAC available upon request.

Standard Model Applications

Model Number: 1002 Type Y
Designation: Purging System
Enclosure Volume: 15 ft³ max.

LPS Style

UL & FM Certified: Cl. I, Div. 1, Group A-D Rating Reduction: Div.1 to Div. 2

WPS Style

UL & FM Certified: Cl. I, Div. 1,

Group C&D Rating Reduction: Div. 1 to Div.2

WPSA Style

UL & FM Certified: Cl. I, Div. 1

Group A-D Rating Reduction: Div. 1 to Div. 2

Model Number:1002 Type ZDesignation:Purging SystemEnclosure Volume:15 ft³ max.

LPS Style

UL & FM Certified: Cl. I, Div. 2, Group A-D

Rating Reduction: Div. 2 to Nonhazardous

WPS Style

UL & FM Certified: Cl. I, Div. 2, Group C&D

Rating Reduction: Div.2 to Nonhazardous


WPSA Style

UL & FM Certified: Cl. I, Div. 2,

Group A-D Rating Reduction: Div. 2 to

Nonhazardous

SERIES



CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM


Material Specifications

Filter Regulator Body: Zinc w/Enamel Finish Regulator Handle & Bowl: **Enclosure Pressure Gauge:** Rapid Exchange Gauge: Tube Fittings & Valves: Tubing: System Nameplates: Fastener Hardware: Mounting Plate: EXP Pressure Switch Body:


Polycarbonate Alum. w/Enamel Finish Poly Case & Brass Tube 316 SS Forged Body 316 SS 1/4" .035 Welded Silk screened Lexan® & SS Alum. & Stainless Steel 316 14 Ga #3 Brush SS Anodized Cast Alum. **Enclosure Warning Nameplate:** Silk screened SS

Lexan® is a registered trademark of the General Electric Company

System Accessories Diagram



Model Number Designations



Model 1002 System Accessories (See accessories page for complete details)

CONNECTION FITTINGS

NC-4 1/4" Ninety Connector SC-4 1/4" Straight Connector EFC-4 1/4" Flush Connector 1/4" Bulkhead Connector EBC-4 EPC-12 3/4" Pipe Connector

ADDITIONAL ITEMS

SMK-2 or -8 System Mounting Kit EPSK-1 Explosion Proof Switch Kit GPSK-1 General Purpose Switch Kit

RAH Remote Alarm Horn RAB-1 Div. 1 Remote Alarm Beacon RAB-2 Div. 2 Remote Alarm Beacon LCK L Fitting Conduit Kit TCK T Fitting Conduit Kit

ENCLOSURE PROTECTION VENTS ONE VENT REQUIRED WITH EACH SYSTEM

EPV-2-SA-00 Straight w/Spark Arrestor EPV-2-SA-90 Rt Angle w/Spark Arrestor

WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning **ETW Enclosure Temperature Warning INSTALLATION & OPERATION MANUAL**

129-0196 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

Overall System Dimensions						
LPS / WPS	LH - left hand	RH - right hand	TM - top mount	BM - bottom mount	WM - wall mount	FM or PM - flat panel
Height	10 / 15	10 / 15	10 / 10	10 / 10	10 / 15	12 / 17
Width	11 / 11	11 / 11	11 / 16	11 / 16	11 / 11	13 / 13
Depth	6 / 7.5	6 / 7.5	6 / 7.5	6 / 7.5	7.75 / 9.25	5 / 6.5

Dimensions in inches. Mounting dimensions available upon request. FM & PM panel cutout dimensions: LPS - 11h x 12w WPS - 16h x 12w Height & Width dimensions reflect mounting plate measurements. Depth dimension reflects overall measurement of system, including components.





Description

Model 1003 is a Rapid Exchange® purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed (protected) enclosure(s), in order to remove and prevent flammable gas or vapor accumulations. The system accomplishes four air exchanges and maintains a "safe" (0.25") pressure. A Pepperl+Fuchs Model EPV-3 Enclosure Protection Vent is required for proper operation. This process reduces the hazardous (classified) area rating within the enclosure(s), in accordance with the NEC - NFPA 70, Article 500, NFPA 496 and ISA 12.4.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. The enclosure protection vent must be tested and the enclosure(s) must be sealed. The enclosure pressure control valve is then used to set a safe reading on the enclosure pressure indicator. When safe pressure is stable, the Rapid Exchange® control valve must be fully engaged. Upon completion of the Rapid Exchange® cycle, (five minutes minimum) the Rapid Exchange® control valve must be disengaged to return to a safe enclosure pressure. Power can then be energized to the protected enclosure(s). Loss of safe pressure requires immediate attention, unless power is deenergized. WPS style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems.

Model 1003



LPS Style (Less Pressure Switch)



WPS/WPSA Style (With Pressure Switch)





System Specifications

System Dimensions: See page 18 Shipping Weight: LPS - 12 lb / WPS - 17 lb -20°F to +120°F Temp. Range: Supply Pressure Range: 80 - 120 psi Capacity & Filtration: 3.8 oz @ 40 Micron Supply Requirements: clean air or inert gas Safe Press. Setpoint: 0.25" Safe Press. Flow Rate: * 0.1 - 3.5 SCFH Exchange Pressure: 3" - 5" Exchange Flow Rate: ** 10 SCFM / 600 SCFH **Exchange Time:** 1 min / 2.5 ft³ System Supply Port: 3/8" FPT **Enclosure Supply Fitting:** 3/8" tube fitting **Enclosure Reference Fitting:** 1/4" tube fitting Switch Setting (Decr): $0.15" \pm 0.02"$ Switch Conduit Port Size: 1/2" FPT Switch Contact Rating WPS Style: 120 VAC, 15 A

* Enclosure integrity determines actual flow rate

*** 120 VAC, 10 A, 28 - 125 VDC

Standard Model Applications


Model Number:	1003 Type Y	Model Number:	1003 Type Z
Designation:	Purging System	Designation:	Purging System
Enclosure Volume:	75 ft³ max.	Enclosure Volume:	75 ft ³ max.
LPS S	tyle	LPS S	ityle
UL & FM Certified:	Cl. I, Div. 1,	UL & FM Certified:	Cl. I, Div. 2,
	Group A-D		Group A-D
Rating Reduction:	Div. 1 to Div. 2	Rating Reduction:	Div. 2 to
WPS S	tyle		Nonhazardous
UL & FM Certified:	Cl. I, Div. 1,	WPS S	Style
	Group C&D	UL & FM Certified:	Cl. I, Div. 2,
Rating Reduction:	Div. 1 to Div. 2		Group C&D
WPSA S	Style	Rating Reduction:	
UL & FM Certified:	Cl. I, Div. 1,		Nonhazardous
	Group A-D	WPSA	Style
Rating Reduction:	Div. 1 to Div. 2	UL & FM Certified:	Cl. I, Div. 2,
			Group A-D
		Rating Reduction:	Div. 2 to
		_	Nonhazardous

Protected under U.S. Patent #5,101,710

WPSA Style:

^{**} With regulator set to 60 psi min. during exchange Rapid Exchange® is a Registered Trademark of Pepperl+Fuchs, Inc.

^{***} Supply voltages 24 VDC and 240 VAC available upon request.




CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM

Material Specifications

Filter Regulator Body: Zinc w/Enamel Finish Regulator Handle & Bowl: Polycarbonate **Enclosure Pressure Gauge:** Alum. w/Enamel Finish Rapid Exchange Gauge: Poly Case & Brass Tube Tube Fittings & Valves: 316 SS Forged Body 316 SS 1/4" & 3/8" .035 Welded Tubing: System Nameplates: Silk screened Lexan® & SS Fastener Hardware: Alum. & Stainless Steel Mounting Plate: 316 14 Ga #3 Brush SS EXP Pressure Switch Body: Anodized Cast Alum. **Enclosure Warning Nameplate:** Silk screened SS

Lexan® is a registered trademark of the General Electric Company

System Accessories Diagram



Model Number Designations

1003 - LPS - CI - YZ - LH - ## Series Model Number -System Style LPS - less pressure switch WPS - with pressure switch
WPSA - with pressure switch **Area Classification** CI - Class I Area **Mounting Configuration** left hand left side of enclosure LH RH right side of enclosure right hand TM - top mount top of enclosure bottom of enclosure BM - bottom mount WM wall surface - wall mount external frame or rack FΜ - frame mount PM - panel mount enclosure surface cutout (Not available in WPS Style) ## - See Accessories Page 116 for additional factory installed accessories

Model 1003 System Accessories (See accessories page for complete details)

Plate

	COM	MECHON	FII II	INGS		
NC-6		3/8"	Nine	ety C	onne	ector
SC-6		3/8" 5	Straiç	ght C	onne	ector
EFC-4		1/4	" Flu	ısh C	onne	ector
EFC-6		3/8	" Flu	ısh C	onne	ector
EBC-6		3/8" Bu	ılkhe	ad C	onne	ector
EPC-13			1" Pi	ipe C	onne	ector
	ADI	DITIONAL	ITE	VIS		
01414	_	_				

SMK-2 or -8 System Mounting Kit EPSK-1 **Explosion Proof Switch Kit**

GPSK-1 General Purpose Switch Kit RAH Remote Alarm Horn RAB-1 Div. 1 Remote Alarm Beacon RAB-2 Div. 2 Remote Alarm Beacon LCK L Fitting Conduit Kit T Fitting Conduit Kit **TCK ENCLOSURE PROTECTION VENTS**

ONE VENT REQUIRED WITH EACH SYSTEM EPV-3-SA-00 Straight w/Spark Arrestor

Rt Angle w/Spark Arrestor

EPV-3-SA-90

WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning **ETW Enclosure Temperature Warning INSTALLATION & OPERATION MANUAL** 129-0195 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

Overall System Dimensions						
LPS / WPS	LH - left hand	RH - right hand	TM - top mount	BM - bottom mount	WM - wall mount	FM or PM - flat panel
Height	12 / 15	12 / 15	12 / 12	12 / 12	12 / 15	14 / 17
Width	11.5 / 11.5	11.5 / 11.5	11.5 / 15.25	11.5 / 15.25	11.5 / 11.5	13.5 / 13.5
Depth	6 / 7.5	6 / 7.5	6 / 7.5	6 / 7.5	7.75 / 9.25	5.75 / 7.25

Dimensions in inches. Mounting dimensions available upon request. FM & PM panel cutout dimensions: LPS - 13h x 12.5w WPS - 16h x 12.5w Height & Width dimensions reflect mounting plate measurements. Depth dimension reflects overall measurement of system, including components.



Description

Model 1004 is a Rapid Exchange® purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed (protected) enclosure(s), in order to remove and prevent flammable gas or vapor accumulations. The system accomplishes four air exchanges and maintains a "safe" (0.25") pressure. A Pepperl+Fuchs Model EPV-4 Enclosure Protection Vent is required for proper operation. This process reduces the hazardous (classified) area rating within the enclosure(s), in accordance with the NEC - NFPA 70, Article 500, NFPA 496 and ISA 12.4.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. The enclosure protection vent must be tested and the enclosure(s) must be sealed. The enclosure pressure control valve is then used to set a safe reading on the enclosure pressure indicator. When safe pressure is stable, the Rapid Exchange® control valve must be fully engaged. Upon completion of the Rapid Exchange® cycle, (five minutes minimum) the Rapid Exchange® control valve must be disengaged to return to a safe enclosure pressure. Power can then be energized to the protected enclosure(s). Loss of safe pressure requires immediate attention, unless power is deenergized. WPS style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems.

Model 1004



LPS Style (Less Pressure Switch)



WPS/WPSA Style (With Pressure Switch)



Model Number



System Specifications

System Dimensions:	See page 20
Shipping Weight:	LPS - 15 lb / WPS - 23 lb
Temp. Range:	-20°F to +120°F
Supply Pressure Range:	80 - 120 psi
Capacity & Filtration:	8.5oz @ 40 Micron
Supply Requirements:	clean air or inert gas
Safe Press. Setpoint:	0.25"
Safe Press. Flow Rate:	* 0.1 - 3.5 SCFH
Exchange Pressure:	3" - 5"
Exchange Flow Rate:	** 30 SCFM /1800 SCFH
Exchange Time:	1 min / 7.5 ft ³
System Supply Port:	1/2" FPT
Enclosure Supply Fitting:	1/2" tube fitting
Enclosure Reference Fitting:	1/4" tube fitting
Switch Setting (Decr):	0.15" ± 0.02"
Switch Conduit Port Size:	1/2" FPT
Switch Contact Rating	
WPS Style:	120 VAC, 15 A

- * Enclosure integrity determines actual flow rate
- ** With regulator set to 80 psi min. during exchange Rapid Exchange® is a Registered Trademark of Pepperl+Fuchs, Inc.

*** 120 VAC, 10 A, 28 - 125 VDC

*** Supply voltages 24 VDC and 240 VAC available upon request.


Standard Model Applications

1004 Type Y | Model Number

Model Number.	1004 Type t	woder wurnber.	1004 Type Z
Designation:	Purging System	Designation:	Purging System
Enclosure Volume:	200 ft ³ max.	Enclosure Volume:	200 ft ³ max.
LPS S	tyle	LPS S	tyle
UL & FM Certified:	Cl. I, Div. 1, Group A-D	UL & FM Certified: Rating Reduction:	CI. I, Div. 2, Group A-D Div. 2 to
Rating Reduction:	Div. 1 to Div. 2		Nonhazardous
WPS S	,	WPS S	Style
UL & FM Certified:	Cl. I, Div. 1, Group C&D	UL & FM Certified:	Cl. I, Div. 2,
Rating Reduction:	Div. 1 to Div. 2	Rating Reduction:	Group C&D Div. 2 to
WPSA S	,	ŭ	Nonhazardous
UL & FM Certified:	Cl. I, Div. 1, Group A-D	WPSA	,
Rating Reduction:	Div. 1 to Div. 2	UL & FM Certified:	Cl. I, Div. 2, Group A-D
		Rating Reduction:	Div. 2 to Nonhazardous

1004 Type 7

WPSA Style:




CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM

Material Specifications


Filter Regulator Body: Zinc w/Enamel Finish Regulator Handle & Bowl: Polycarbonate **Enclosure Pressure Gauge:** Alum. w/Enamel Finish Rapid Exchange Gauge: Poly Case & Brass Tube 316 SS Forged Body Tube Fittings & Valves: 316 SS 1/4" & 1/2" .035 Welded Tubing: System Nameplates: Silk screened Lexan® & SS Fastener Hardware: Alum. & Stainless Steel Mounting Plate: 316 14 Ga #3 Brush SS **EXP Pressure Switch Body:** Anodized Cast Alum. **Enclosure Warning Nameplate:** Silk screened SS

Lexan® is a registered trademark of the General Electric Company

System Accessories Diagram



Model Number Designations



Model 1004 System Accessories (See accessories page for complete details)

Plate

CONNECTION FITTINGS

NC-8 1/2" Ninety Connector SC-8 1/2" Straight Connector EFC-4 1/4" Flush Connector EFC-8 1/2" Flush Connector EBC-8 1/2" Bulkhead Connector 1 1/2" Pipe Connector EPC-14 **ADDITIONAL ITEMS**

SMK-2 or 8 System Mounting Kit EPSK-1 Explosion Proof Switch Kit

GPSK-1 General Purpose Switch Kit RAH Remote Alarm Horn RAB-1 Div. 1 Remote Alarm Beacon RAB-2 Div. 2 Remote Alarm Beacon LCK L Fitting Conduit Kit T Fitting Conduit Kit **TCK ENCLOSURE PROTECTION VENTS**

ONE VENT REQUIRED WITH EACH SYSTEM

EPV-4-SA-00 Straight w/Spark Arrestor EPV-4-SA-90 Rt Angle w/Spark Arrestor


WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning **ETW Enclosure Temperature Warning INSTALLATION & OPERATION MANUAL** 129-0203 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

Overall System Dimensions						
LPS / WPS	LH - left hand	RH - right hand	TM - top mount	BM - bottom mount	WM - wall mount	FM or PM - flat panel
Height	12 / 16.25	12 / 16.25	12 / 12	12 / 12	12 / 15	14 / 18.25
Width	13.5 / 13.5	13.5 / 13.5	13.5 / 16.75	13.5 / 16.75	13.5 / 13.5	15.5 / 15.5
Depth	6.75 / 8.25	6.75 / 8.25	6.75 / 8.25	6.75 / 8.25	7.75 / 9.25	6.75 / 8.25
D:	DI					

Dimensions in inches. Mounting dimensions available upon request. FM & PM panel cutout dimensions: LPS - 13h x 14.5w WPS - 17.25h x 14.5w Height & Width dimensions reflect mounting plate measurements. Depth dimension reflects overall measurement of system, including components.





Class I (\leq 90 ft³) and Zone 2 (\leq 2.54m³)

Description

Model 3003 is a Rapid Exchange® purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed protected enclosure(s), in order to remove and prevent flammable gas or vapor accumulations. The Model 3003 consists of three major components: (1) a pneumatic manifold assembly, (2) a differential enclosure pressure indicator and (3) a stainless steel face plate with mounting flange, or a Lexan® system start up instruction nameplate. Model 3003 is offered in three distinct variations, identified as "VM" (Vertical Mount), "HM" (Horizontal Mount), both available in WPS & WPSA styles, and "CK" (Component Kit) mounting configurations. The VM configuration features a filter regulator and face plate with a flange for mounting to a vertical surface. The HM configuration features a regulator and face plate with a flange for mounting on a horizontal surface. Finally, the CK configuration is a kit of parts including the pneumatic manifold assembly, the enclosure pressure indicator and a start-up instruction nameplate. The VM and HM configurations are intended for flange or frame mounting to a solid surface on or near the protected enclosure(s), while the CK configuration is intended for frame mounting through cutouts in a panel on or near the enclosure(s). With the addition of a Model GCK gauge conversion kit, all configurations can be mounted through the surface of a protected enclosure. The CK configuration provides a seal that withstands type 4 hosedown testing. Model 3003 accomplishes the required volume exchanges and maintains a safe pressure. Pepperl+Fuchs Model EPV-3 enclosure protection vent is required for proper operation. This process reduces the hazardous (classified) area rating within protected enclosure(s), in accordance with the NEC - NFPA 70, NFPA 496, ISA 12.4 and IEC 600 79-15 EN 50021.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. The enclosure protection vent must be tested and enclosure(s) must be sealed. After transferring the valve key, locked into the pneumatic manifold's Rapid Exchange® control valve stem, the enclosure pressure control valve is used to set a safe reading on the enclosure pressure indicator. When safe pressure is stable, the valve key is transferred and locked into the Rapid Exchange® control valve stem and the Rapid Exchange® control valve is then fully engaged. Upon completion of the Rapid Exchange® cycle, (five minutes minimum) the Rapid Exchange® control valve is disengaged to return to a safe enclosure pressure. Power can then be energized to the protected enclosure(s). Loss of safe pressure requires immediate attention, unless power to the protected enclosure(s) is deenergized. WPS and WPSA style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems.

Rapid Exchange® is a Registered Trademark of Pepperl+Fuchs, Inc. Lexan® is a registered trademark of the General Electric Company

Model 3003





Model 3003-LPS-CI-YZ-VML **Vertical Mount Configuration**

Model 3003-WPS-CI-YZ-HMT **Horizontal Mount Configuration**







Model 3003-LPS-CI-YZ-CK Component Kit Configuration









3003

Standard Model Applications

Model Number: 3003 Type Y System Designation: Rapid Exchange® Purging **Enclosure Volume:** 90 ft³ (2.54m3) max. LPS Style UL & FM Certified: Cl. I, Div. 1, Group A-D Rating Reduction: Div. 1 to Div. 2 **WPS Style** UL & FM Certified: Cl. I, Div. 1, Group C-D Rating Reduction: Div. 1 to Div. 2 **WPSA Style** Cl. I, Div. 1, UL & FM Certified: Group A-D

Model Number: Type Z and Ex [nP] System Designation: Rapid Exchange® Purging **Enclosure Volume:** 90 ft³ (2.54m3) max. LPS Style UL & FM Certified: Cl. I, Div. 2, Group A-D ATEX 'nP' Certified: Zone 2, Group IIC Rating Reduction: Div. 2 to Nonhazardous Zone 2 to Nonhazardous WPS Style UL & FM Certified: Cl. I. Div. 2.

Group C-D

Rating Reduction: Div. 2 to Nonhazardous

WPSA Style

UL & FM Certified: Cl. I, Div. 2, Group A-D ATEX 'nP' Certified: Zone 2, Group IIB+H Rating Reduction: Div. 2 to Nonhazardous Zone 2 to Nonhazardous


> (ξx) II 3G EEx [nP] II Protected under U.S. Patent #5,101,710



SERIES

Model 3003 VM Configuration - The Vertical Mount System


LPS (Less Pressure Switch)




Important Notes

- 1) The HM configuration is supplied with a mounting flange for right-angled attachment to a horizontal surface external to the protected enclosure.
- 2) The VM configuration can also be frame mounted external to the protected enclosure through a 5" (127mm) W x 9" (229mm) H cutout in a suitable mounting surface.
- 3) Model GCK gauge conversion kit is required to panel mount the VM configuration through a 5" (127mm) W x 9"(229mm) H cutout in the protected enclosure surface.
- 4) See page 36 for Model GCK kit description and conversion procedure.

WPS / WPSA (With Pressure Switch)






CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM



Model 3003 HM Configuration - The Horizontal Mount System


LPS (Less Pressure Switch)



Important Notes

- 1) The HM configuration is supplied with a mounting flange for right-angled attachment to a horizontal surface external to the protected enclosure.
- 2) The HM configuration can also be frame mounted external to the protected enclosure through a 10.25" (260mm) W x 5" (127mm) H cutout in a suitable mounting surface.
- 3) Model GCK gauge conversion kit is required to panel mount the HM configuration through a 10.25" (260mm) W x 5" (127mm) H cutout in the protected enclosure surface.
- 4) See page 36 for Model GCK kit description and conversion procedure.

WPS / WPSA (With Pressure Switch)




CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM



SERIES


Model 3003 CK Configuration - The Component Kit System



Important Notes

- 1) The CK configuration is four discrete parts suitable for mounting through a set of cutouts in a vertical surface external to the protected enclosure.
- 2) A Model GCK gauge conversion kit is required to panel mount the CK configuration through a set of cutouts in the protected enclosure surface.
- 3) See page 36 for Model GCK kit description and conversion procedure.

CK Configuration System & Optional Remote Cube Filter Dimensions in Inches (mm)





Model 3003 WPS VM Configuration & Flange Dimensions in Inches (mm)

LPS (Less Pressure Switch)


Panel Cutout | \$ (127) | \$ | | \$ (127) | \$ | | \$ (2141.3) | | \$ (228.6) | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ | | \$ (25.5) | \$ |

VM Configuration Front View

Panel Cutout

4.0 (101.6) 1.5 (38.1)

VM Configuration Side View




Vertical Mount Flange Front View


WPS/WPSA VM Configuration Front View

4.0 (101.6) 3.5 (88.9)

WPS/WPSA (With Pressure Switch)




WPS/WPSA VM Configuration Side View



WPS/WPSA Vertical Mount Flange Front View

Model 3003 HM Configuration & Flange Dimensions in Inches (mm)


LPS (Less Pressure Switch)



LPS HM Configuration Front View




LPS HM Configuration Side View




LPS Horizontal Mount Flange Front View


WPS/WPSA (With Pressure Switch)



WPS/WPSA HM Configuration Front View



WPS/WPSA HM Configuration Side View



WPS/WPSA Horizontal Mount Flange Front View




SERIES

Typical Model 3003 System Installation Details


External to the Protected Enclosure

Flange Mount HM Configuration with Model SMK-1 Fastener Kit



Internal to the Protected Enclosure


Panel Mount CK Configuration with Model RCF-4 Remote Cube Filter & Model GCK Gauge Conversion Kit




Standard and Panel Mount Pneumatic Installation Diagram

Standard Pneumatic Installation Diagram

See panel mounting conversion procedure on page 36



Panel Mount Installation Diagram





VM Configuration Mounting Options



Model 3003-LPS-CI-YZ-VML Flange Mounted to Flat Vertical Surface with Model SMK-1 Fastener Kit



Model 3003-LPS-CI-YZ-VML Flange Mounted to Vertical 2" Pipe Stand with Model PMK-1 Fastener Kit




Model 3003-LPS-CI-YZ-VM Frame or Panel* Mounted **Through Cutout in Suitable Surface** with Model SMK-6m Fastener Kit

HM Configuration Mounting Options



Model 3003-LPS-CI-YZ-HMT Flange Mounted to Flat Horizontal Surface with Model SMK-1 Fastener Kit



Model 3003-LPS-CI-YZ-HMB Flange Mounted to Horizontal 2" Pipe Stand with Model PMK-1 Fastener Kit



Model 3003-LPS-CI-YZ-HM Frame or Panel* Mounted Through Cutout in Suitable Surface with Model SMK-6m Fastener Kit

CK Configuration Mounting Options



Front View



Rear View


Model 3003-LPS-CI-YZ-CK Rear View of Frame or Panel* Mount Through Cutout in Suitable Surface with supplied fasteners

PANEL MOUNTED SYSTEMS REQUIRE A PEPPERL+FUCHS MODEL GCK FOR PROPER OPERATION - SEE PAGE 36



SERIES

Model 3003 Panel Mount Conversion



Standard Configuration (prior to conversion) (after conversion)

Panel Mount Configuration

- 1. Secure one Model GCK Conversion Kit. Kit includes a PRB-4 & SC-2 Fitting & Enclosure Pressure Gauge gasket.
- 2. Remove venturi orifice and run tee from the high port of the gauge and discard.
- 3. Remove sintered vent from low port.
- 4. Reinstall sintered vent into high port.
- 5. Install Model SC-2 fitting into low port.
- 6. Install Gauge gasket between gauge & mounting surface.
- 7. Install Model PRB-4 fitting through enclosure surface (vent end out) and connect tubing (customer supplied) between SC-2 & PRB-4.

Material Specifications

Regulator Body: Regulator Handle & Bowl*: **Enclosure Pressure Gauge:** Rapid Exchange® Gauge: Tube Fitting: Tubing: Fastener Hardware: System Face Plate: System Mounting Flange: Manifold Body: Manifold Valves: Mfr. ID Nameplate: **Enclosure Warning Nameplate: EXP Pressure Switch Body:**

Zinc w/Enamel Finish Polycarbonate Alum. w/Enamel Finish Poly & Nickel Plated 316 SS Forged Body 316 SS 1/4" .035 Welded Alum. & Stainless Steel 316 14 Ga #3 Brush SS 316 SS Tumble Finish **Anodized Aluminum** 316 Stainless Steel Silkscreen Lexan® Silk screened SS **Anodized Cast Aluminum**

Lexan® is a registered trademark of the General Electric Company

System Specifications

System Dimensions: See pages 32-33 Shipping Weight: LPS - 10 lb (4.5 kg) / WPS - 15 lb (6.8 kg)

-20°F to +120°F (-29°C to +49°C) Temp. Range: Supply Pressure Range: 80 - 120 psi (5.5 - 8.3 bar) Capacity & Filtration: 1.5 oz @ 20 Micron Supply Requirements: clean air or inert gas Safe Press. Setpoint: 0.25" (6.35mm) Safe Press. Flow Rate: * 0.1 - 3.5 SCFH (2.8 - 99 I/hr) **Exchange Pressure:** * 3" - 5" (76.2 mm - 127 mm) Exchange Flow Rate: ** 12 SCFM /720 SCFH (340 I/m / 20390 I/hr)

Exchange Time:

1 min / 3.0 ft3 (85 I/min) 4 Volume Exchange Rate: 5 Volume Exchange Rate: 1 min / 2.4 ft³ (68 I/min) 1/2" FPT System Supply Port: **Enclosure Supply Port:** 1/2" FPT **Enclosure Reference Fitting:** 1/4" Tube Switch Setting (WPS & WPSA Only): 0.15" ± 0.02"

3.81mm ± 0.51 mm 1/2"FPT

Switch Conduit Port Size: Switch Contact Ratings:

WPS Style: 120 VAC, 15 A WPSA Style: *** 120 VAC, 10 A, 28 - 125 VDC

Enclosure integrity determines actual flow rate With regulator set to 60 psi min. during exchange Supply voltages 24 VDC and 240 VAC available upon request.

Model Number Designations

3003 - LPS - CI - YZ - VM - ## Series Model Number -System Style LPS - less pressure switch WPS - with pressure switch WPSA - with pressure switch **Area Classification** - Class I Area System Type - Div. 1 to Div. 2 Div. 2 / Zone 2 to Nonhazardous **Mounting Configuration** VML - vertical mount left left of enclosure VMR - vertical mount right right of enclosure **HMT** - horizontal mount top top of enclosure HMB - horizontal mount bottom bottom of enclosure CK - Component Kit - LPS style only ## - See Accessories Page 117 for additional factory installed accessories † Does not have ATEX certification

Model 3003 System Accessories (See accessories page for complete details)

NC-6-4 3/8" T x 1/4" P Ninety Connector SC-6-4 3/8" T x 1/4" P Straight Connector NC-6-8 3/8" T x 1/2" P Ninety Connector SC-6-8 3/8" T x 1/2" P Straight Connector EFC-4 1/4" Flush Connector EBC-4 1/4" Bulkhead Connector EFC-6 3/8" Flush Connector FBC-6 3/8" Bulkhead Connector

CONNECTION FITTINGS

ADDITIONAL ITEMS

SMK-1 System Mounting Kit - Flange SMK-6m System Mounting Kit - Frame/Panel PMK-1 Pipe Mounting Kit **GCK** Gauge Conversion Kit ILF-4 1/4" In-Line Filter Kit RCF-4 1/4" Remote Cube Filter EPSK-1 **Explosion Proof** Switch Kit (GRP C, D) EPSK-1A **Explosion Proof** Switch Kit (GRP A-D) GPSK-1 General Purpose Switch Kit **RAH** Remote Alarm Horn Div. 1 Remote Alarm Beacon RAB-1 RAB-2 Div. 2 Remote Alarm Beacon **ENCLOSURE PROTECTION VENTS**

ONE VENT REQUIRED WITH EACH SYSTEM

EPV-3-SA-00 Straight w/Spark Arrestor EPV-3-SA-90 Rt Angle w/Spark Arrestor

WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning ETW **Enclosure Temperature Warning INSTALLATION & OPERATION MANUAL** 129-0198 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

Protected under U.S. Patent #5,101,710

EPC-13



1 1/4" Pipe Connector

^{*} Refers to filter bowl supplied with VM mounting configuration.

Class I (\le 250 ft³) and Zone 2 (\le 7.08m³)

Description

Model 3004 is a Rapid Exchange® purging system that operates on a supply of compressed instrument air or inert gas. It regulates and monitors pressure within sealed protected enclosure(s), in order to remove and prevent flammable gas or vapor accumulations. The Model 3004 consists of three major components: (1) a pneumatic manifold assembly, (2) a differential enclosure pressure indicator and (3) a stainless steel face plate with mounting flange, or a Lexan® system start up instruction nameplate. Model 3003 is offered in three distinct variations, identified as "VM" (Vertical Mount), "HM" (Horizontal Mount), both available in WPS & WPSA styles, and "CK" (Component Kit) mounting configurations. The VM configuration features a filter regulator and face plate with a flange for mounting to a vertical surface. The HM configuration features a regulator and face plate with a flange for mounting on a horizontal surface. Finally, the CK configuration is a kit of parts including the pneumatic manifold assembly, the enclosure pressure indicator and a start-up instruction nameplate. The VM and HM configurations are intended for flange or frame mounting to a solid surface on or near the protected enclosure(s), while the CK configuration is intended for frame mounting through cutouts in a panel on or near the enclosure(s). With the addition of a Model GCK gauge conversion kit, all configurations can be mounted through the surface of a protected enclosure. The CK configuration provides a seal that withstands type 4 hosedown testing. Model 3004 accomplishes the required volume exchanges and maintains a safe pressure. Pepperl+Fuchs Model EPV-3 enclosure protection vent is required for proper operation. This process reduces the hazardous (classified) area rating within protected enclosure(s), in accordance with the NEC - NFPA 70, NFPA 496, ISA 12.4 and IEC 600 79-15 EN 50021.

Operation

In accordance with system instructions, start-up requires air supply to be engaged and enclosure power to be deenergized. The enclosure protection vent must be tested and enclosure(s) must be sealed. After transferring the valve key, locked into the pneumatic manifold's Rapid Exchange® control valve stem, the enclosure pressure control valve is used to set a safe reading on the enclosure pressure indicator. When safe pressure is stable, the valve key is transferred and locked into the Rapid Exchange® control valve stem and the Rapid Exchange® control valve is then fully engaged. Upon completion of the Rapid Exchange® cycle, (five minutes minimum) the Rapid Exchange® control valve is disengaged to return to a safe enclosure pressure. Power can then be energized to the protected enclosure(s). Loss of safe pressure requires immediate attention, unless power to the protected enclosure(s) is deenergized. WPS and WPSA style systems include an explosion proof differential pressure switch with form "C" contacts for audible or visual alarm systems

Rapid Exchange® is a Registered Trademark of Pepperl+Fuchs, Inc.

Model 3004





Model 3004-LPS-CI-YZ-VML Vertical Mount Configuration

Model 3004-WPS-CI-YZ-HMT Horizontal Mount Configuration







Model 3004-LPS-CI-YZ-CK Component Kit Configuration



Model Number:







Standard Model Applications

3004

Type Y System Designation: Rapid Exchange® Purging **Enclosure Volume:** 250 ft3 (7.08m³) max. LPS Style UL & FM Certified: Cl. I, Div. 1, Group A-D Rating Reduction: Div. 1 to Div. 2 WPS Style Cl. I, Div. 1, UL & FM Certified: Group C-D Rating Reduction: Div. 1 to Div. 2 WPSA Style UL & FM Certified: Cl. I, Div. 1, Group A-D Rating Reduction: Div. 1 to Div. 2

Model Number: 3004 Type Z and Ex [nP] System Designation: Rapid Exchange® Purging **Enclosure Volume:** 250 ft3 (7.08m³) max. LPS Style UL & FM Certified: Cl. I, Div. 2, Group A-D ATEX 'nP' Certified: Zone 2, Group IIC Rating Reduction: Div. 2 to Nonhazardous Zone 2 to Nonhazardous **WPS Style** UL & FM Certified: Cl. I, Div. 2, Group C-D Rating Reduction: Div. 2 to Nonhazardous WPSA Style UL & FM Certified: Cl. I, Div. 2, Group A-D ATEX 'nP' Certified: Zone 2,

Rating Reduction:

Protected under U.S. Patent #5,101,710

Zone 2 to Nonhazardous

Group IIB+H,


Div. 2 to Nonhazardous



SERIES

Model 3004 VM Configuration - The Vertical Mount System


LPS (Less Pressure Switch)




Important Notes

- 1) The VM configuration is supplied with a mounting flange for right angle-attachment to a vertical surface external to the protected enclosure.
- 2) The VM configuration can also be frame mounted external to the protected enclosure through a 5" (127mm) W x 10.75" (273mm) H cutout in a suitable mounting surface.
- 3) Model GCK gauge conversion kit is required to panel mount the VM configuration through a 5" (127mm) W x 10.75" (273mm) H cutout in the protected enclosure surface.

WPS / WPSA (With Pressure Switch)






CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM



Model 3004 HM Configuration - The Horizontal Mount System


LPS (Less Pressure Switch)



Important Notes

- 1) The HM configuration is supplied with a mounting flange for right-angled attachment to a horizontal surface external to the protected enclosure.
- 2) The HM configuration can also be frame mounted external to the protected enclosure through a 10.25" (260mm) W x 5.5" (140mm) H cutout in a suitable mounting surface.
- 3) Model GCK gauge conversion kit is required to panel mount the HM configuration through a 10.25" (260mm) W x 5.5" (140mm) H cutout in the protected enclosure surface.
- 4) See page 44 for Model GCK kit description and conversion procedure.

WPS / WPSA (With Pressure Switch)



CONNECTION POINTS SHOWN ABOVE IN BOLD TEXT ON SYSTEM DIAGRAM




Reference

3000

SERIES

Model 3004 CK Configuration - The Component Kit System




Important Notes

- 1) The CK Configuration is four discrete parts suitable for mounting through a set of cutouts in a vertical surface external to the protected enclosure.
- 2) A Model GCK gauge conversion kit is required to panel mount the CK configuration through a set of cutouts in the protected enclosure surface.
- 3) See page 44 for Model GCK kit description and conversion procedure.

Orifice

CK Configuration System & Optional Remote Cube Filter Dimensions in Inches (mm)








Model 3004 WPS VM Configuration & Flange Dimensions in Inches (mm)

LPS (Less Pressure Switch)

VM Configuration Front View

4.0 (101.6) 1.5 (38.1)


VM Configuration Side View




Vertical Mount Flange Front View

Panel Cutout 7.5 (190.5) Panel Cutout 13.5 (242.9) 8 (203.2)

WPS/WPSA VM Configuration Front View




WPS/WPSA VM Configuration Side View



WPS/WPSA Vertical Mount Flange Front View

Model 3004 HM Configuration & Flange Dimensions in Inches (mm)


LPS (Less Pressure Switch)



LPS HM Configuration Front View




LPS HM Configuration Side View



LPS Horizontal Mount Flange Front View


WPS/WPSA (With Pressure Switch)



WPS/WPSA HM Configuration Front View



WPS/WPSA HM Configuration Side View



WPS/WPSA Horizontal Mount Flange Front View




SERIES

Typical Model 3004 System Installation Details


External to the Protected Enclosure

Flange Mount HM Configuration with Model SMK-1 Fastener Kit



Internal to the Protected Enclosure


Panel Mount CK Configuration with Model RCF-8 Remote Cube Filter & Model GCK Gauge Conversion Kit




Standard and Panel Mount Pneumatic Installation Diagram

See panel mounting conversion procedure on page 44

Standard Pneumatic Installation Diagram



Panel Mount Installation Diagram





VM Configuration Mounting Options



Model 3004-LPS-CI-YZ-VML Flange Mounted to Flat Vertical Surface with Model SMK-1 Fastener Kit



Model 3004-LPS-CI-YZ-VML Flange Mounted to Vertical 2" Pipe Stand with Model PMK-1 Fastener Kit




Model 3004-LPS-CI-YZ-VM Frame or Panel* Mounted Through Cutout in Suitable Surface with Model SMK-6m Fastener Kit

HM Configuration Mounting Options



Model 3004-LPS-CI-YZ-HMT Flange Mounted to Flat Horizontal Surface with Model SMK-1 Fastener Kit



Model 3004-LPS-CI-YZ-HMB Flange Mounted to Horizontal 2" Pipe Stand with Model PMK-1 Fastener Kit



Model 3004-LPS-CI-YZ-HM Frame or Panel* Mounted Through Cutout in Suitable Surface with Model SMK-6m Fastener Kit

CK Configuration Mounting Options



Front View



Rear View


Model 3004-LPS-CI-YZ-CK
Rear View of Frame or Panel* Mount
Through Cutout in Suitable Surface with supplied fasteners

* PANEL MOUNTED SYSTEMS REQUIRE A PEPPERL+FUCHS MODEL GCK FOR PROPER OPERATION - SEE PAGE 44



SERIES

Model 3004 Panel Mount Conversion



Standard Configuration (prior to conversion) (after conversion)

Panel Mount Configuration

- 1. Secure one Model GCK Conversion Kit, kit includes a PRB-4 & SC-2 Fitting & Enclosure Pressure Gauge gasket.
- 2. Remove venturi orifice and run tee from the high port of the gauge and discard.
- 3. Remove sintered vent from low port.
- 4. Reinstall sintered vent into high port.
- 5. Install Model SC-2 fitting into low port.
- 6. Install Gauge gasket between gauge & mounting surface.
- 7. Install Model PRB-4 fitting through enclosure surface (vent end out) and connect tubing (customer supplied) between SC-2 & PRB-4.

System Specifications

System Dimensions: See pages 40-41 Shipping Weight: LPS-12 lb (5.4 kg) WPS-17 lb (7.7 kg)

Temp. Range: -20°F to +120°F (-29°C to +49°C) Supply Pressure Range: 80 - 120 psi (5.5 -8.3 bar) Capacity & Filtration: 8.5 oz @ 40 Micron Supply Requirements: clean air or inert gas 0.25" (6.35mm) Safe Press. Setpoint: Safe Press. Flow Rate: * 0.1 - 3.5 SCFH (2.8 - 99 I/hr) Exchange Pressure: * 3" - 5" (76.2mm - 127mm) ** 30 SCFM /1800 SCFH Exchange Flow Rate: (850 1/m / 50976 1/hr)

Exchange Time:

4 Volume Exchange Rate: 1 min / 7.5 ft³ (212.4 I/m) 5 Volume Exchange Rate: 1 min / 6.0 ft³ (169.9 *I*/m) System Supply Port: 1/2" FPT **Enclosure Supply Port:** 1/2" FPT **Enclosure Reference Fitting:** 1/4" Tube Switch Setting (WPS & WPSA Only): 0.15" ± 0.02"

 $(3.81 \text{mm} \pm 0.51 \text{mm})$ 1/2"FPT

Switch Conduit Port Size: Switch Contact Ratings:

WPS Style: 120 VAC, 15 A *** 120 VAC, 10 A, 28 - 125 VDC WPSA Style:

- * Enclosure integrity determines actual flow rate
- ** With regulator set to 60 psi min. during exchange
- *** Supply voltages 24 VDC and 240 VAC available upon request.

Material Specifications

Regulator Body: Regulator Handle & Bowl*: **Enclosure Pressure Gauge:** Rapid Exchange® Gauge: Tube Fitting: Tubing: Fastener Hardware: System Face Plate: System Mounting Flange: Manifold Body: Manifold Valves: Mfr. ID Nameplate: **Enclosure Warning Nameplate:**


EXP Pressure Switch Body:

Polycarbonate Alum. w / Enamel Finish Poly & Nickel Plated 316 SS Forged Body 316 SS 1/4" .035 Welded Alum. & Stainless Steel 316 14 Ga #3 Brush SS 316 SS Tumble Finish **Anodized Aluminum** 316 Stainless Steel Silkscreen Lexan® Silk screened SS **Anodized Cast Aluminum**

Zinc w/Enamel Finish

Refers to filter bowl supplied with VM mounting configuration. Lexan® is a registered trademark of the General Electric Company

Model Number Designations



factory installed accessories † Does not have ATEX certification

Model 3004 System Accessories (See accessories page for complete details)

	CONNECTION FITTINGS		
NC-8	1/2" T x 1/2" P Ninety Connector		
SC-8	1/2" T x 1/2" P Straight Connector		
EFC-4	1/4" Flush Connector		
EBC-4	1/4" Bulkhead Connector		
EFC-8	1/2" Flush Connector		
EBC-8	1/2" Bulkhead Connector		
EPC-14	1 1/2" Pipe Connector		
ADDITIONAL ITEMS			

CONNECTION FITTINGS

SMK-1 System Mounting Kit - Flange SMK-6m System Mounting Kit - Frame/Panel

PMK-1 Pipe Mounting Kit GCK Gauge Conversion Kit ILF-8 1/2" In-Line Filter Kit 1/2" Remote Cube Filter RCF-8 EPSK-1 **Explosion Proof** Switch Kit (GRP C, D) FPSK-1A **Explosion Proof** Switch Kit (GRP A-D) GPSK-1 General Purpose Switch Kit RAH Remote Alarm Horn Div. 1 Remote Alarm Beacon RAB-1 RAB-2 Div. 2 Remote Alarm Beacon

ENCLOSURE PROTECTION VENTS

ONE VENT REQUIRED WITH EACH SYSTEM

EPV-4-SA-00 Straight w/Spark Arrestor EPV-4-SA-90 Rt Angle w/Spark Arrestor

WARNING NAMEPLATES

EWN-1 Class I Enclosure Warning **Enclosure Temperature Warning INSTALLATION & OPERATION MANUAL**

129-0216 Inst. & Operation Manual

ONE (1) ENCLOSURE WARNING NAMEPLATE & ONE (1) INSTALLATION & OPERATION MANUAL ARE PROVIDED WITH EACH SYSTEM

